



easy to install, easy to program,
easy to use



Dialock DFT Furniture Locking System



How Dialock DFT works?



1. Hold programmed key close to the reader.



2. A signal will be sent to the concealed DFT-terminal, which releases the lock(s) that the key is authorised to open. Then open the drawer, glass sliding door, etc.



3. ... take out or place object closing the drawing or glass display will automatically re-lock it.

The Product

Dialock DFT is a touch-free identification and locking system. It replaces the combination of mechanical keys and locks completely and offers a significantly greater range of functions. Dialock is very flexible and can be extended at any time, from one to multiple users. The DFT identification and locking system is made up of three basic components with one of three Locking Device options:

- Electronic keys
- + Dialock furniture terminal - DFT
- + 12 VAC power supply
- + Locking device - FLC for all hinged doors and drawers or
- Locking device - EFL3 for all applications including doors and drawers with soft-close

Conventional keys are replaced by an electronic key. The key contains a memory chip on which user data and access authorisations are stored.

Dialock DFT can be used on:

- Drawers
- Cabinet doors
- Glass doors
- Sliding doors
- Display cabinets
- Wall cabinets
- Shutters
- and many more

Diallock DFT Complete Sets



PS power supply unit
237.58.140



Buzzer audible
237.56.140



DFT/B V2 furniture terminal
237.58.111



LED visual
237.56.141



Distributor
823.28.780



MLA 8 multi-lock adapter
910.51.083



MLA 6 multi-lock adapter
910.51.083












MLA 8 multi-lock adapter
910.51.084



FLC lock
237.56.002













EFL 3 lock
237.56.304
+ 237.56.343

			Technology system	Colour	Cat. No.
		KT key tag	Tag-it™ ISO Diallock Standard	White	917.44.107
				Black	917.44.103
				Grey	917.44.105
				Red	917.44.109
				Blue	917.44.108
				Orange	917.44.101
		KT user card			917.44.020
		Key fob		Grey	917.44.085
 		Signal buzzer			237.56.140
		Setup alarm feature			N/A
 		LED light			237.56.141
		Drilling jig for FLC lock			237.56.990



Components

Image	Technology	Description	Article no.
	Lock FLC FLC without feedback contact, with plastic bolt	Cable length 3 m	237.56.002
	Lock EFL 3 For hinged door, soft close and push runner	Without cable for DFT/B	237.56.304
	Cable V2 For connecting the EFL 3	Cable length 3 m	237.56.343
	Terminal DFT/B V2 Tag-it™ ISO processor	Dialock standard	237.58.111
	Antenna 3 m	Cable length 3 m	237.58.129
	Power supply unit	Output current 2 A	237.58.140
	Distributor For connecting max, 6 furniture locks to the DFT furniture terminal	Output current 2 A	823.28.780
	Adapter MLA 6 key alike	MLK 6 multi-lock adapter	910.51.083
	Adapter MLA 8 key difference	MLA 8 multi-lock adapter	910.51.084
	Programming card For Tag-it™ ISO processor	Size 54 x 85 mm	917.42.001
	Deletion card For Tag-it™ ISO processor	Size 54 x 85 mm	917.42.002

Dialock DFT Furniture Locking System



Application Examples:

1. Shops

Sophisticated shop-fitting for high-quality jewellery or watch display, which require uncompromising design solutions with a high degree of functionality and security

2. Offices

Protect your documents from unauthorised access. Dialock DFT allows you to open and lock your office furniture locks in an instant. Just one programmed key for all furniture locks.

3. Hospitals and Doctor's Surgery

If the doctor has to leave the room for a moment, medicines and records are kept safe in treatment rooms, consulting rooms and receptions. One key for all furniture locks.





Head Office

PT Häfele Indotama

Taman Tekno BSD Blok A No. 3

Serpong, Tangerang 155314

Indonesia

Phone + 62 21 7587 8888

Fax + 62 21 7587 7777

info@hafele.co.id

www.hafele.com / www.hafele.co.id

Central Java

Jl. Lampersari No.15

Semarang 50249

Phone: +62 24 864 54 301

Fax: +62 24 864 54 302

smg@hafele.co.id

Yogyakarta

Jl. Wonosari, Ruko Tandan Raya B6

Yogyakarta 55198

Phone: +62 274 451 660

Fax: +62 274 451 660

yogya@hafele.co.id

East Java

Jl. Mayjend Sungkono 176 - 178

Ruko Grand Sungkono Blok A-8

Surabaya 60189

Phone: +62 31 5680 800

Fax: +62 31 5670 800

sby@hafele.co.id

Bali

Jl. Bypass Ngurah Rai 120 i

Kuta 80361

Phone: +62 361 764 278

Fax: +62 361 759 995

dpr@hafele.co.id

HÄFELE

www.hafele.co.id

732.98.11004